

TINY with urine tube

Size matters.

The latest toilet solution from Separetts is the small and fleixble, Tiny. A real friend to Tiny Houses and other small places. Choose between two versions and think about what you should do with all the space that you will get.


- Tiny with urine tube: internal collection of solid waste. external collection of urine
- Tiny with urine container: internal collection of urine and solid waste This leaflet describes Tiny with urine tube

EASY TO USE



OPTIMIZED FOR TINY SPACES

After several years of development of urine diverting toilets this has led to the simple and flexible design of Separett Tiny that is a perfect fit for small spaces. Especially developed for Tiny Homes and other small spaces such as camper vans, caravans, boats, hunting cottages etc.



HIGH CAPACITY

Thanks to the urine separation, both the smell and the volume of the waste that must be disposed of are reduced.

The solid waste is collected in the solid waste container inside of the toilet whilst the urine is led to an external container. through a urine tube.



VIEW SCREEN

The view screen hides the solid waste in the container and is pushed to the side when you sit down to use the toilet. This results in that you only see the toilet waste when it is time to empty the solid waste.



HYGENIC AND ODORLESS

The operational reliability of Tiny is high and the installation of the toilet is easy. The fan exhales the small odor that is formed, despite urine separation, and contributes to a better indoor climate by constantly keeping the air in the space in motion.

INCLUDED WITH TINY 1270-01

Instructions for use, Installation manual, Battery cables for 12 V use, Universal adapter for 110-240 V use, 1 \times latrine container with lid, urine tube, Ø 32 mm urine hose 2 m, Ø 32 mm straight joint, Ø 32 mm 90 degree joint, Cover plate for wall bushing \emptyset 32 mm, 2 x wall brackets for urine pipe, \emptyset 50 mm ventilation tube 40 cm, Adapter Ø 50 mm - 1 1/2", Ventilation grille with insect net, Ventilation cowl, Holder for drain cleaning tablet, Silicone for sealing, Installation sketch, Screws for wall / floor, 10 compostable bags, Bio drain cleaner sample, Absorb pad sample, Filter for ventilation pipes

SUPPLEMENT WITH

Urine-diverting child seat 1101



Enabling even the smallest ones to use the urine diverting toilet.

Bio drain cleaner 1118



Bio drain cleaner keeps the urine drain free from urine salts that can clog the urine hose.

Absorb Tiny 1346



The Absorb pad is placed in the bottom of the waste bag and is used to soak up any moisture coming from the waste

INSTALLATION

All that is needed for installing Tiny with urine tube is the electric energy of 12 V or 110–240 V, a 50 mm ventilation pipe that is used for ventilating the toilet and a urine hose from a 32mm pipe in the back of the toilet to lead the urine out to an external container.

The toilet is designed for 50 mm ventilationpipes (outer diameter). For optimal function it is recommended that you use Separett's own installation kit that has pipes and angles in the correct dimensions. Separett Tiny can be installed with up to 5 meters of ventilation piping and 2 90-degree bends. Ventilated air can go through a wall, floor or roof, for example, up into an attic and out through a suitable side of the house.


To install the urine hose without visible pipes, the 90-degree bend is used to guide the urine downwards or the straight joint to go backwards as shown in the picture to the right.

Installation example



TECHNICAL DATA

TINY	Material	container	Voltage/ Wattage	Power consumtion	Electrical connection	Noise level Max weight	Max weight
	Recyclable high-gloss poly- propylene	Inner container solid waste: 14,5 L polypropylene	12 V / 1.6 W	0.04 kWh/day	61" alt. Universal power adapter 110/230V-12V	<30dB(A)	150 kg



Connections:

Ventilation out: Ø 51mm Urine out: Ø 33mm



